Raytronics AG

Wärmeschrumpftechnik

Heat shrink tube, FEP, 1.6 to 1, high temperature tubing

The heat shrinking tubes FEP are made of fluorinated ethylene propylene. These heat shrink tubes are used for versatile electronical applications. The outstanding UV-resistance and high-clarity enable an outdoor installation. These tubes can be sterilised by Gamma, ETO, e-beam and autoclave sterilisation what makes them very popular for medical applications. Compared to PTFE, these FEP heat shrink tubes has a lower shrink temperature.



- 1.6 to 1 shrink ratio
- Excellent dielectric strength
- Biocompatible
- Chemical resistance
- High optical clarity
- Sterilisable
- High working temperature (+200°C)

Specifications and Approvals of heat shrink tube FEP

- UL94 V-0
- Compliant to AMS-DTL-I-23053/11
- USP Class VI on request

Dimensions in mm

Part Number	Inside Diameter		Wall Thickness	Reel
	As Supplied	After Heating	After Heating +/- 5%	in Meter
FEP-3/32-X-S	2.36	1.42	0.20	+/- 0.08
FEP-1/8-X-S	3.18	1.91	0.25	+/- 0.08
FEP-3/16-X-S	4.78	2.92	0.25	+/- 0.08
FEP-1/4-X-S	6.35	3.81	0.25	+/- 0.08
FEP-3/8-X-S	9.53	5.72	0.31	+/- 0.08
FEP-1/2-X-S	12.7	7.62	0.38	+/- 0.1
FEP-3/4-X-S	19.05	11.43	0.51	+/- 0.1
FEP-1-X-S	25.40	15.24	0.64	+/- 0.13
FEP-1-1/2-X-S	38.10	22.86	0.76	+/- 0.13
FEP-2-X-S	50.8	30.48	0.76	+/- 0.13

Standard Colour

Colour	Clear / Natural	
Ordering Code	х	

This datasheet is issued without guarantee according to the correctness of the containing information, product and service descriptions. The data has been carefully checked, Raytronics AG is not liable for any loss or damage resulting from errors or omission in hereby contained information.



Temperature

Operating range Min. shrinking temperature +205°C +190°C